

# MILITARY SPECIFICATION DOLPHICAM2+ PRODUCT SPECIFICATION

The dolphicam2+ is capable of high-resolution imaging and precise measurements for a wide range of material types including composites, metals and multi materials.

With a straightforward, quick to deploy, user-friendly system, technicians of all experience levels can generate analysis-ready images of materials in real time for quick decision making.

### **MILITARY MODES AVAILABLE**

Adapted specifically for military use; with all connectivity (Wi-Fi and Bluetooth) disabled and no camera.

dolphitech.com

## **Black Box and Rugged Tablet**

The dolphicam2+ consists of a rugged 14" DT340T tablet with a combined table stand and Black Box mounting bracket on its rear.

A kick stand allows you to prop your device at almost any angle that's convenient for you.

Weighing less than 5kg and with the 40% larger screen size than the dolphicam2, it makes the DC2+ ideally suited for in service and manufacturing inspections.



### Features

- Anti-glare screen
- Can connect to external PC
- 🔗 Audio buzzer

### Size and weight

Tablet, Black Box	
and TRM	5.2kg / 11.2lb
Size (combined)	376 x 244 x 61mm
Size (Black Box)	200 x 130 x 32mm
Size (tablet)	376 x 244 x 29mm

### **Technical details**

Transducer ports Other connections Battery Ingress protection PC/Host port

Ethernet 6-8 hours IP66 USB C

2x USB C

# The tablet has a daylight-readable display with gloved-multitouch and waterproof digitizer pen.

05830 PC	i i U	-
15820 AUX	6	101
<b>F</b> 12	dolphicam2	102
m		1

The Black Box itself is the heart of the system, driving the TRM while connecting to the tablet which runs and displays the software.


The IP66 sealing gives the device full protection against dust, and also protects against low pressure water jets from all directions.

The tablet is equipped with an Intel<sup>®</sup> 8th Generation Core™ i quad-core processor.




### **Software**

The dolphicam2+ software is unique among NDT packages, designed from the ground up to complement the imaging capabilities of the platform. Ultrasonic images are shown not just using conventional signal amplitudes, but also as time of flight, opening up a world of instant, color-coded thickness mapping. This is helped further by the live 3D characterization view, which instantly enhance visualization and can be readily interpreted by different levels of end-users.




#### **Measurements**

- Depth B-scan
- Line in C-scan
- Depth & Amplitude in C-scan
- Rectangle (Width, Height, Area)
- Circle (Diameter, Circumference Area)



### **Views**

- A-scan
- B-scan (vertical/ horizontal, TFM)
- C-scan (Amplitude, ToF)
- 3D (ToF & Amp)
- Stitch view



### **Features**

- Live 1 Axis & 2 Axis Encoded Mapping
- Grid and free hand stitching
- Configuration setting files
- Full Matrix Capture (FMC)
- ✓ Total Focusing Method (TFM)
- CO TCG Functionality
- Digital Time Corrected Gain (TCG)
- Report configuration
- Defect Detection
- Histogram Statistical Data Graph  $(\checkmark)$

### **Other General Funcionality**


- Color focus
- Reset settings to default
- Save screenshot
- **Remote TRM activation**
- Expanded view (hide config menu)
- Comfortable handle for portability
- On board, simple to use calibration function

For maximum image quality we also provide Total Focusing Method (TFM) reconstructions, with TFM images available on both vertical and horizontal B-scan views.



### **Specification**

Data transfer rate	Up to 3.2 Gbit/s depending on transducer settings	
Effective data acquisition rate	30 full data sets (128x128 A-scans) per second with typical settings	
Data processing	Low pass filter, data sampling, Total Focusing Method	
Visualization	Single element signals (A-scans), vertical cross sections (B-scans), horizontal cross sections and material thickness mappings (C-scans) and 3D.	
Adjustable settings	Measurement unit, material depth, gating, material sound velocity, transmit pulse shape, gain, filtering and averaging, time corrected gain, color palette	
Statistical data	Mean (+Std. Deviation), Median, and Mode	
Data file format	Open, HDF5 based file format	
Time Corrected Gain (TCG)	0 to 10 dB/µs	
Digital Gain	+50dB	
Averaging	1 - 16	
Delay	1 - 82 µs	
Depth	1 - 120 mm @ 6,000 m/s	
Velocity	100 - 20.000 @ 6,000 (list of velocity)	
Gates	3 separate gates	
Amplitude threshold	Threshold for each gate	
Capture method (for C-scan)	Max Absolute / Negative / Positive	
A/B Scan Mode (RF)	Full, Absolute. Envelope	
Color palettes	(Jet, gray, grav-inv, autumn bone, winter, rainbow, ocean, summers,	
	spring, hsv, pink, hot, customizable)	
Image filter	None, gaussian, median	



# **MORE INFORMATION**

Want to learn more about what you can do with the dolphicam2+

Contact us to arrange a 10-minute demonstration with one of our expert consultants to understand how you can utilize dolphicam2+

sales@dolphicam.com

